

00213180

Component


MPZ1300-LN-10-00-P-P-FA-FA

14483-28

Serial number

Packaging-interfacesInput fiberPolarization maintaining, Panda typeOutput fiberPolarization maintaining, Panda typeJacket type900µm outside diameterInput optical connector (orientation)FC/APCKey // slow axisKey // slow axisOutput fiber length1.5 meterOutput fiber length1.5 meterInput RF port50Ω, female K

Product dimension and pin-out



Thickness : 9.6mm Material : KOVAR Package dimensions in mm

Measured with : Gooch & Housego DFB model λ = 1310 nm

Parameters	Conditions		Measurements	Specifications
Insertion Loss	with input connection	dB	3,4	≤3.75
Vp RF Port	@50kHz	V	4,0	≤4
Electrical return loss S11	between 0 – 10GHz	dB	-15,6	≤-13
Electro-optic bandwidth S21	@ -3dB, from 2GHz	GHz	>10	>10

Position	Name/Visa	Date
Test engineer	A.BAUD	2024-02-27

Precautions of use :

For bias control and modulation signal, please refer to the Application Note "LiNbO3 Intensity Modulators Bias Control and Modulation Driving". This application note aims to give intensity modulators users the basics to select and apply the proper RF and bias voltages to their device and can be downloaded from our company website www.photonics.ixblue.com

In order to avoid any damage to the modulator and to keep its performance at maximum, please pay a special attention to the following :

When handling the modulator, do not apply any excessive tensile strength neither bend on the fiber pigtails.

•• Always keep the optical connectors end face protected and clean the optical connector end face with appropriate tissue before

••• Clean RF connector with dry air before mating and use a torque wrench for tightening.

•••• Respect maximum ratings mentioned in accordance with specifications (www.exail.com/event_category/photonics.com)

••••• At the maximum optical power, fusion splices are expressly recommended to avoid permanent damage on optical connectors.

•••••• In the case of optical instabilities, when operating at high optical power or shorter wavelength, it might be necessary to heat up the modulator (max 50°C)



EXAIL, Photonic Solutions Division 3, rue Sophie Germain 25000 Besançon, France Tél : +33 1 30 08 88 88 Fax : +33 1 30 08 88 00